

Elapsed Timer Button Kit (V1.0)


Features:

Twelve buttons for various applications

Larger Buttons for Code Blue and Stop functions

Ordering Information:

SBD-ELT-BUT-0



The buttons themselves do not contain programming or configuration code. To make the elapsed timer perform the function described on the button, the clock connected to the control panel must be reconfigured. For Wired-IP and Wi-Fi clocks, this can be done through the clock's web interface. For all other digital clocks, this can be done using USB programming cable D-USB485-INTF-1.

More information regarding button programming is available in the Elapsed Timer manual. The manual can be found at <https://sapling-inc.com/manuals>.

Only one of each button type shown is provided per kit. For duplicate buttons, please purchase duplicate kits.

Specification sheets may change without prior notice